# **Clamp Gaskets**


#### **Specifications**

• PSI Service Ratings for the sanitary clamps DO NOT APPLY to connections (1" and above) using any PTFE gaskets, due to the potential for cold flow under normal operating conditions. PTFE gaskets, when used with any clamp, are likely to leak at pressures far below the published service ratings. This restriction does not apply to the fractionally sized 1/2" and 3/4" connections, due to their recessed, fully contained design.


#### **Approva**

• Gasket material approved by (3A), USDA and complies with FDA's 21CFR177.2600 and 1550









**Clamp Gaskets - Black** 



Type 1 - Standard 1" and larger



Type 1 - Standard 1/2" - 3/4"

#### **Feature**

· Color code: one red dot

### **Approval**

Meets 21CFR 177.2600

Size	Nitrile Rubber Part #
1/2"	42MP-U50
3/4"	42MP-U75
1"	40MP-U100
1-1/2"	40MP-U150
2"	40MP-U200
2-1/2"	40MP-U250
3"	40MP-U300
4"	40MP-U400
5"	40MP-U500
6"	40MP-U600
8"	40MP-U800

# **Clamp Gaskets - White**



Type 1 - Standard 1" and larger



Type 1 - Standard 1/2" - 3/4"

#### **Feature**

· Color code: one red dot

#### **Approval**

• Meets 21CFR 177.2600

Size	Nitrile Rubber Part #
1/2"	42MP-UW50
3/4"	42MP-UW75
1"	40MP-UW100
1-1/2"	40MP-UW150
2"	40MP-UW200
2-1/2"	40MP-UW250
3"	40MP-UW300
4"	40MP-UW400
6"	40MP-UW600

## **Clamp Gaskets - Black**



Type 1 - Standard 1" and larger



Type 1 - Standard 1/2" - 3/4"

# Features

- · Color code: three green dots
- · Peroxide cured

## **Approvals**

- Meets 21CFR 177.2600
- Passed U.S.P. Class VI Cytotoxicity testing

Size	EPDM Part #
1/2"	42MP-E50
3/4"	42MP-E75
1"	40MP-E100
1-1/2"	40MP-E150
2"	40MP-E200
2-1/2"	40MP-E250
3"	40MP-E300
4"	40MP-E400
5"	40MP-E500
6"	40MP-E600

Visit canada.dixonvalve.com for sizing charts.